



WD-90GR, TOUCH FLEX

POT DISHWASHER

(with or without granules)

- Efficient frontloaded potwasher, washes pots and pans with or without granules.
- The WD-Touch display guides you through the washing process with an intuitive touch screen. Easy navigation with built-in user manuals.
- Excellent washing results and fast drying with efficient and energy saving centrifuging spin cycle.
- Perfect for space efficient installations
- No manual pre-wash or scrubbing thanks to heavy rinsing with water and granules.
- Stacking of goods can be made directly on the hinged door.
- Square washing cassette for containers, holds eight 1/2 or four 1/1 containers.
- Wide range of accessories for various items.
- Accessories for washing 65 and 40 mm-deep 2/1 containers and baking trays 600x400 mm.
- Hinged door enables for easy cleaning.
- Six different wash programs with HACCP function.
- Service can easily be made from the front or side
- Accessories incl in delivery: 1 pc square cassette, 3 pcs support wall, 3 pcs side holder, 1 pc flexibel insert, cleaning scraper and granules 2x5 kg.



OPTIONS

- Condensing unit ECO-FLOW
- Marine version 400V/3/50 without neutral
- Marine version 440V/3/60 without neutral
- Steam heated design, pressure 50-250 kPa
- Booster pump
- Break tank incl. booster pump
- Stainless couplings in the final rinse
- Connection power restriction
- Connection power restriction SICOTRONIC
- External power indication
- Web Tool with HACCP documentation and consumption report
- Drain pump

EXTRA EQUIPMENT

- Table trolley
- Dockable loading trolley 900 mm 209.7454
- Holder for accessories, to be placed on the side of the machine
- Square cassette 209.7296 (1 pc included in the delivery)
- Cassette for canteens with handles
- Cassette for large boxes
- Basket for 4 pc GN 1/1-canteens - 200 mm deep
- Granules 2x5 kg (included in the delivery)
- Cleaning scraper (1 pc included in the delivery)

ACCESSORIES FOR CASSETTES

- All-round holder 209.7273
- Holder for utensils 209.7277
- Wire basket for small utensils 209.7278
- Holder for small pots 209.7279
- Support wall 209.7280 (1 pc included in the delivery)
- Flexible insert, 209.7281, to be used together with 209.7354
- Holder for 1/3, 1/6 and 1/9 containers. 209.7282
- Holder for 1/4, 1/6 containers 209.7286
- Side holder 209.7354
- Rubber strap 209.7272

TECHNICAL DATA	WD-90GR TOUCH FLEX
Granule wash pump (kW)	2.2
Wash pump (kW)	1.5
Motor for the round table (kW)	0,18
Booster heater (kW)	9
Heater tank (kW)	9
Tank volume (litres)	100
Weight, machine in operation (kg)	430
Granule volume (kg)	5
Degree of protection (IP)	IP55

CAPACITY AND OPERATION DATA	WD-90GR TOUCH FLEX
Total time/wash program 1** (min) washing with granules, with spin (can be excluded by technician)	5
Total time/wash program 2** (min) washing with granules, with spin (can be excluded by technician)	8
Total time/wash program 3** (min) washing with granules, with spin (can be excluded by technician)	10.3
Total time/wash program 4** (min) washing without granules, with spin (can be excluded by technician)	2.3
Total time/wash program 5** (min) washing without granules, with spin (can be excluded by technician)	3.8
Total time/wash program 6** (min) washing without granules, with spin (can be excluded by technician)	6.8
Capacity, max (1/1 containers/program)****	4
Capacity, max (1/2 containers/program)****	8
Capacity / h, Pr 1 (1/1-containers) incl. handling ****(pc)	45
Capacity / h, Pr 1 (1/2-containers) incl. handling ****(pc)	90
Water consumption rinse/program (litres) *****	3.5-5

CAPACITY AND OPERATION DATA	WD-90GR TOUCH FLEX
Water consumption cooling/program (litres) *****	0-1.5
Energy consumption (kWh of connected power)	70-90%
Steam consumption *** (kg/h)	15
Sound level* (dB(A)) washing program with granules	69
Max. surface temp. at room temp. 20°C (°C)	30

* A-weighted sound pressure level, LpA

** Factory setting. The wash time is adjustable

*** Steam heated machine

**** Max. capacity depending on the depth of the containers.

***** Applies program using spinning. The water consumption depends on local conditions. An exact adjustment is made during installation.

CONNECTION, ELECTRICALLY HEATED MACHINE	WD-90GR TOUCH FLEX
Total connected power (kW)	11.3
Main fuse 400V 3N~ (A)*	20
Max.conn.area 400V 3N~ (L1-L3,N,PE) Cu (mm²)	6

* Other voltages on request

CONNECTION, STEAM HEATED MACHINE 50-250 KPA	WD-90GR TOUCH FLEX
Total conn.power (kW)	2.4
Main fuse 400V 3N~(A)*	16
Max.conn.area 400V 3N~(L1-L3, N, PE) Cu (mm²)	6
Steam connection (internal thread)	R½"
Connection condense water (internal thread)	R½"

* Other voltages on request

CONNECTION WATER, DRAIN AND VENTILATION	WD-90GR TOUCH FLEX
Water quality, hardness (°dH)	2 - 7
Cold water connection 5-12°C (internal thread)	R½"
Hot water connection 50-65°C (internal thread)	R½"
Drain connection, PP pipe (ø mm)	50
Water capacity warm water, pressure (kPa)	250
Water capacity warm water, flow (litres/min)	15
Water capacity cold water cooling, min/max pressure (kPa)	100/160
Floor drain, capacity (litres/sec)	3
Ventilation of the machine (m³/h)	600

SIZE AND WEIGHT FOR TRANSPORTATION	WD-90GR TOUCH FLEX
Size * LxWxH (mm)	1060x900x1950
Weight * (kg)	340

* Packaging included

ACCESSORIES FOR WD-90GR TOUCH FLEX



*Square shaped cassette, part. no. 209.7276
Included in the delivery.*



*Side holder, part. no. 209.7354
3 pcs included in the delivery.*



*Lid holder, part. no. 209.7280
3 pcs included in the delivery.*



*Flexible insert, part. no. 209.7281
Used together with side holder.
Included in the delivery.*



Utensil holder, part. no. 209.7277



Wire basket, part. no. 209.7278



*Allround holder, part. no. 209.7273
For pots with handles and ABC-
containers.*





*Holder for 1/3, 1/6, 1/9 containers,
part. no. 209.7282*



Sous vide basket. part. no. 209.7291

The above accessories are a selection of Wexiödisk range. Additional equipment for other kind of dishes can be requested.



- 1. Cold water connection
- 2. Hot water connection
- 3. Electrical connection
- 4. Steam connection (steam-heated machine)
- 5. Condensation water connection (steam-heated machine)
- 6. Drain connection
- 7. Detergent connection

We reserve the right to change technical data.

Wexiödisk^W

TELEPHONE: +46 470 77 12 00 FAX: +46 470 237 52 ADDRESS: Mårdvägen 4 SE-352 45 Växjö SWEDEN
E-MAIL: wexiodisk@wexiodisk.com WEBB: www.wexiodisk.com